StarTech.com

Hard-to-find made easy®

25U Rack Enclosure



Actual product may vary from photos

User Manual

SKU#: RK2537BKM

For the latest information and specifications visit
www.startech.com/RK2537BKM

Manual Revision: 07/01/2026

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

Safety Statements

Safety Measures

- Wiring terminations should not be made with the product and/or electric lines under power.
- Product installation and/or mounting should be completed by a certified professional as per the local safety and building code guidelines.
- Cables (including power and charging cables) should be placed and routed to avoid creating electric, tripping or safety hazards.

Mesures de sécurité

- Les terminaisons de câblâge ne doivent pas être effectuées lorsque le produit et/ou les câbles électriques sont sous tension.
- L'installation et/ou le montage du produit doit être réalisé par un professionnel certifié et dans le respect des normes locales et du code de construction local.
- Les câbles (y compris les câbles d'alimentation et de chargement) doivent être placés et acheminés de façon à éviter tout risque électrique, de chute ou de sécurité

安全対策

- 電源が入っている状態の製品または電線の終端処理を行わないでください。
- 製品の設置やマウントは、使用地域の安全ガイドラインおよび建築基準に従い、有資格の専門業者が行うようにしてください。
- ケーブル（電源ケーブルと充電ケーブルを含む）は、適切な配置と引き回しを行い、電気障害やつまづきの危険性など、安全上のリスクを回避するようにしてください。

Misure di sicurezza

- I terminiali dei fili elettrici non devono essere realizzate con il prodotto e/o le linee elettriche sotto tensione.
- L'installazione e/o il montaggio dei prodotti devono essere eseguiti da un tecnico professionale certificato che conosca le linee guida locali sulle norme edilizie e sulla sicurezza.
- I cavi (inclusi i cavi di alimentazione e di ricarica) devono essere posizionati e stesi in modo da evitare pericoli di inciampo, rischi di scosse elettriche o pericoli per la sicurezza.

Säkerhetsåtgärder

- Montering av kabelavslutningar får inte göras när produkten och/eller elledningarna är strömförda.
- Installation och/eller montering får endast göras av behöriga yrkespersoner och enligt gällande lokala förordningar för säkerhet och byggnormer.
- Kablar (inklusive elkablar och laddningskablar) ska dras och placeras på så sätt att risk för snubblingsolyckor och andra olyckor kan undvikas.

Warning Statements

- Make sure that you assemble this product according to the instructions.
- Do not exceed the weight capacity of this product. Overloading this product might result in injury or property damage. This product can support the following weight: Stationary: 2866lbs. (1300 kg) and Rolling 2006.21lbs (910 kg)
- This product is intended for indoor use only and should not be used outdoors.
- This enclosure is extremely heavy. Never attempt to move or lift this enclosure without assistance.
- Tipping hazard! Extending multiple components from this enclosure increases the chance that the enclosure will tip over. To avoid this risk, do not extend more than one component from the enclosure.
- Do not place any items on this enclosure and do not stack the enclosure on top of another enclosure.
- Keep liquid away from this enclosure.
- Make sure that you install the enclosure in an area that can handle the combined weight of the enclosure and the equipment that you intend to place inside of the enclosure.
- This product requires an earth ground connection. Do not use this product without an earth ground connection.

Varningsmeddelanden

- Se till att du monterar produkten i enlighet med instruktionerna.
- Överskrid inte produktens viktkapacitet. Överbelastning av produkten kan orsaka skada på person eller egendom. Denna produkt har stöd för följande vikter: 1300 kg.
- Produkten är endast avsedd för användning inomhus och ska inte användas utomhus.
- Detta skåp är extremt tungt. Försök aldrig flytta på skåpet eller lyfta det utan hjälp.

- Risk för vältning! Att förlänga flera komponenter från detta skåp ökar risken för att det välter. Förläng inte fler än en komponent från skåpet för att undvika risk.
- Placera inte saker ovanpå skåpet och ställ inte skåpet ovanpå ett annat skåp.
- Håll vätskor borta från skåpet.
- Se till att du installerar skåpet på en plats som kan hantera den kombinerade vikten av skåpet och utrustningen som du tänker placera inuti.
- Produkten behöver en jordad anslutning. Använd inte produkten utan en jordad anslutning.

Avertissements

- Assemblez ce produit conformément aux instructions.
- Ne dépassez pas la capacité pondérale du produit. Une surcharge du produit peut entraîner des blessures ou des dommages matériels. Ce produit peut supporter 1300 kg.
- Ce produit est uniquement destiné à une utilisation en intérieur et ne doit pas être utilisé à l'extérieur.
- Ce rack de serveur est extrêmement lourd. Ne tentez jamais de le déplacer ou de le soulever sans aide.
- Risque de basculement ! L'extension de plusieurs composants à partir du rack de serveur augmente le risque de basculement. Pour éviter ce risque, n'étendez pas plus d'un composant à partir du rack de serveur.
- Ne placez aucun objet sur ce rack de serveur et n'empilez pas le rack sur un autre rack.
- N'approchez aucun liquide du rack de serveur.
- Veillez à installer le rack de serveur dans un endroit pouvant supporter le poids combiné du rack et des équipements que vous comptez placer à l'intérieur.
- Ce produit nécessite un raccordement à la terre. N'utilisez pas ce produit sans raccordement à la terre.

Warnhinweise

- Beachten Sie bei der Montage dieses Produkts die Montageanweisungen.
- Überschreiten Sie nicht die Tragkraft dieses Produkts. Ein Überladen dieses Produkts kann zu Verletzungen oder zur Beschädigung des Produkts führen. Dieses Produkt ist für folgendes Gewicht geeignet: 1300 kg.
- Dieses Produkt ist nur zum Gebrauch in Innenräumen vorgesehen und sollte nicht im Freien verwendet werden.
- Dieses Gehäuse ist extrem schwer. Versuchen Sie niemals, dieses Gehäuse ohne Hilfe zu bewegen oder anzuheben.
- Kippgefahr! Das Ausziehen mehrerer Komponenten aus diesem Gehäuse

erhöht die Chance, dass das Gehäuse umkippt. Um dies zu vermeiden, ziehen Sie niemals mehr als eine Komponente aus diesem Gehäuse aus.
- Platzieren Sie keine Gegenstände auf dem Gehäuse und stapeln Sie das Gehäuse nicht auf einem anderen Gehäuse.
- Halten Sie Flüssigkeiten von diesem Gehäuse fern.
- Vergewissern Sie sich, dass der Untergrund, auf dem das Gehäuse aufgestellt wird, in der Lage ist, das Gesamtgewicht des Gehäuses und der Geräte, die Sie darin platzieren möchten, zu tragen.
- Dieses Produkt erfordert einen Schutzleiteranschluss. Verwenden Sie das Produkt nicht ohne einen Schutzleiteranschluss.

Dichiarazioni di avvertenza

- Assicurarsi di Assemblare il prodotto secondo le istruzioni.
- Non superare la capacità di carico del prodotto. Il sovraccarico del prodotto potrebbe causare danni o lesioni. Il prodotto è in grado di supportare i seguenti pesi: 1300 kg.
- Il prodotto è destinato all'uso in ambienti interni. Se ne sconsiglia l'impiego in ambienti esterni.
- Il box esterno è molto pesante. Non tentare di spostarlo o sollevarlo senza assistenza.
- Pericolo di ribaltamento! L'estensione di più componenti dal box esterno aumenta il rischio di ribaltamento del box esterno. Per evitare questo rischio, non estendere più di un componente dal box esterno.
- Non collocare oggetti sul box esterno e non impilare un box esterno sopra un altro.
- Tenere il box esterno lontano dai liquidi.
- Assicurarsi di installarlo in un punto che possa sorreggere il peso combinato del box esterno e dell'apparecchiatura che si intende collocare al suo interno.
- Il prodotto richiede una messa a terra. Non utilizzare il prodotto in assenza di una messa a terra.

Mensagens de aviso

- Certifique-se de que monta este produto de acordo com as instruções.
- Não exceda a capacidade de peso deste produto. Sobrecarregar este produto pode resultar em ferimentos ou danos de propriedade. Este produto pode suportar o seguinte peso: 1300 kg.
- Este produto destina-se apenas a uma utilização no interior e não deve ser utilizado no exterior.
- Esta caixa é extremamente resistente. Nunca tente mover ou levantar esta caixa sem assistência.
- Perigo de queda! Estender vários componentes desta caixa aumenta a

probabilidade desta caixa cair. Para evitar este risco, não expandir mais de um componente desta caixa.
- Não colocar nenhum artigo nesta caixa e não empilhar a caixa em cima de outra caixa.
- Manter líquidos afastados desta caixa.
- Certifique-se de que instala a caixa numa área que pode suportar o peso combinado da caixa e o equipamento que pretende colocar dentro da caixa.
- Este produto requer uma ligação à terra. Não utilize este produto sem uma ligação à terra.

Advertencias de uso

- Asegúrese de ensamblar este producto según las instrucciones.
- Asegúrese de no exceder la capacidad de peso de este producto. La sobrecarga de este producto puede causar lesiones personales o daños en la propiedad. Este producto tiene capicidad para el siguiente peso: 1300 kg.
- El uso de este producto es solo para interiores y no debe utilizarse en exteriores.
- La caja es extremadamente pesada. Nunca intente mover o alzar esta caja sin la debida asistencia de otra persona.
- ¡Peligro de vuelco! Añadir a esta caja varios componentes aumenta las posibilidades de peligro de vuelco de la caja. Para evitar dicho riesgo, no añada más que un solo componente.
- No coloque ningún elemento encima de la caja y no apile la caja encima de otra caja.
- Mantenga cualquier líquido lejos de la caja.
- Asegúrese de instalar la caja en un área que tenga capacidad para soportar el peso combinado de la caja y el equipo que va a instalar dentro de la misma.
- Este producto requiere conexión a tierra. No utilice este producto sin conexión a tierra.

Waarschuwingen

- Zorg dat u dit product volgens de instructies in elkaar zet.
- Overschrijd de maximale capaciteit van dit product niet. Overbelasting van dit product kan letsel of materiële schade veroorzaken. Dit product ondersteunt het volgende gewicht: 1300 kg.
- Dit product is alleen bedoeld voor binnengebruik en mag niet buiten worden gebruikt.
- Deze behuizing is enorm zwaar. Probeer nooit deze behuizing te verplaatsen of op te tillen zonder hulp.
- Kantelgevaar! Wanneer meerdere componenten uit deze behuizing steken, bestaat de kans dat deze zal kantelen. Om dit risico te voorkomen, mag niet

meer dan één component uit de behuizing steken.
- Plaats geen voorwerpen op deze behuizing en stapel de behuizing niet op een andere behuizing.
- Houd vloeistof uit de buurt van deze behuizing.
- Zorg dat u de behuizing installeert op een plaats die geschikt is voor het gecombineerde gewicht van de behuizing en de apparatuur die u in de behuizing wilt plaatsen.
- Dit product vereist een geaarde verbinding. Gebruik dit product niet zonder een geaarde verbinding.

注意

必ず取扱説明書に従って本製品の組み立てを行って下さい。

本製品で定められた最大積載重量を超えないようにして下さい。最大積載重量をオーバーした場合、怪我をする恐れや器物破損の恐れがあります。本製品は、モニター1台あたり1300kgまで支持できます。

本製品は、室内での使用を想定しています。戸外では使用しないで下さい。

本製品は、非常に重いエンクロージャです。絶対に一人で持ち上げたり動かしたりしないで下さい。

転倒注意！本製品から複数のコンポーネントが突き出した状態にしておくとエンクロージャが転倒する恐れがあります。転倒リスクを回避するために、エンクロージャからはコンポーネントが突き出ないようにして下さい。

本製品の上に何も載せないで下さい。複数のエンクロージャを重ねて設置しないで下さい。

液体物をエンクロージャに近づけないようにして下さい。

エンクロージャ自身と中に積載する装置の総重量に耐えられるエリアに設置して下さい。

この製品にはアースが必要です。アース接続をしていない状態で本製品を使用しないでください。

Table of Contents

Safety Statements 2
Safety Measures 2

Warning Statements 3

Product Information 9
Package Contents 11
Requirements 11


Unpacking the Rack 12

Installation 14
Leveling the Rack 14


Installing the Cage Nuts 15
Removing the Front and/or Rear Door 16
Reversing the Front Door 17
Removing the Side Panels 19
Installing the Side Panels 21
Removing the Roof Panel 22
Grounding the Rack 23
Adjusting the Vertical Mounting Rails or Cable Management Rails 23
Baying Multiple Racks Together 26

Product Diagram (RK2537BKM)

Front View



Side View


966 mm (38.03")
Locking Latch
Side Panel
992 mm (39.06")
1156.35 mm (45.53")
1068.40 mm (42.06")

Product Information

Package Contents

- Server Rack Cabinet x 1
- M6 Cage Nuts x 104
- M6 Screws x 104
- A Pair of Keys x 1
- Hex Key x 1
- 10 ft (3 m) Hook-and-Loop Tape x 1
- Plastic Cup Washers x 104
- User Manual x 1

Requirements

For the latest requirements, please visit www.startech.com/RK2537BKM

Installation:

The following Items required for installation are sold separately.

- Wrench x 1
- 13 mm Socket x 1
- Level x 1
- Grounding Wire x 1
- Phillips Head Screwdriver x 1

Unpacking the Rack

Warnings: *The* **Rack** *is heavy and you should exercise caution when you remove it from the* **Pallet***.*

At least three people are required to unpack the **Rack***. Do not attempt to unpack the* **Rack** *by yourself.*

1. Carefully move the shipping **Pallet** to a level surface.
2. Remove the **Tie Straps** from the **Shipping Carton**.
3. Remove the **Shipping Carton** from the shipping **Pallet**, **13 mm Socket** and **Wrench**, remove the Bolts from the Pallet Brackets.



Removing the Bolts

Note: *Make sure that at least one person is holding the* **Rack** *in place while removing the* **Pallet Brackets***.*


4. Carefully remove the **Rack** from the **Pallet** and place it on a firm surface.

Installation

Leveling the Rack

The **Rack** will need to be properly level prior to the installation of any **Rack Equipment**, to ensure stability. The surface the **Rack** is located must also be flat and level to support the weight of the **Rack** and **Rack Equipment** installed.

1. Determine the location of the **Rack**. Once this location is determined, use the **Level** to ensure that the surface is a flat level surface.
2. Using an **14mm Open-Ended Wrench**, lower one of the **Levelers** by turning it clockwise until the base of the **Leveler** is tightly pressed against the surface, supporting the weight of the Rack.



Levelers

3. Place the **Level** on the top of the **Rack** to ensure that the **Levelers** are adjusted correctly. If the **Rack** is not level make the required adjustments to the **Levelers** until the **Rack** is Level.

Securing the Rack to the Floor

You can use the **Pallet Brackets** and **Bolts** used to secure the **Rack** to the shipping **Pallet** to securely fasten the **Rack** to the floor.

1. Align the two **Pallet Brackets** with the **Bracket Holes** on the bottom of the **Rack's Door Frame**. The **Pallet Brackets** can be mounted on the exterior or interior of the **Rack**.
2. Using a **13 mm Socket** and **Wrench**, insert two of the **Bolts** through the **Pallet Bracket** and into the **Rack**.
3. Insert the other two **Bolts** through the **Pallet Bracket** and into the surface you are securing the **Rack** to.

   Note: *Pilot holes may need to be drilled in the surface you are securing the* **Rack** *to, prior to installing the* **Pallet Brackets**.

Installing the Cage Nuts

Note: *When installing equipment in the* **Rack**. *Start at the bottom of the* **Rack** *with the heaviest equipment and work your way to the top.*

1. Determine the U-space of your equipment and where in the **Rack** you want to install the device.
2. Apply pressure to both sides of the **Cage Nut**. Insert the **Cage Nut Clamps** into the **Cage Nut Hole** and release the **Cage Nut**.
   - or -

   Use the included **Cage Nut Wrench** to install the **Cage Nuts** into the **Rack**.
3. Use the **M6 Screws** to secure the **Device** into place.

4. If your **Device** has mounting brackets with hooks, hook the bracket to the position.

Removing the Front and/or Rear Door

Note: *At least two people are required when removing or reinstalling the door from the* **Rack**.

1. Unplug the **Grounding Wire** connecting the **Door** to the **Door Frame**. The **Grounding Wire** is located in the top inside corner of the door.



Grounding Wire

2. With the **Door** open at a 90-degree angle to the **Rack Frame**, lift the **Door** from out of its hinges and pull outward to remove it from the **Rack Frame**.

Note: *To reinstall the* **Door** *reverse the steps above.*


Reversing the Front Door

1. Unplug the grounding wire connecting the door to the door frame. The grounding wire is located in the top inside corner of the door.





2. With the door open at a 90-degree angle to the rack frame, lift the door from out of its hinges and pull outward to remove it from the door frame.




3. Remove the screw and washer from the rear of the door handle, remove the latching mechanism. Reverse the latch, so it points in the opposite direction, then use the screw and washer to re-attach the latch to the rear of the door handle. Reinstall the handle.





4. Remove the door frame hinges from the rack frame, rotate them 180 degrees and attach them on the opposite side of the rack frame.



5. Remove the door hinges from the door, and reattach to another position.





6. Reinstall the door. Remember to connect the grounding wire.

Removing the Side Panels

Note: *At least two people are required when removing or reinstalling the* **Side Panel** *from the* **Rack**.

1. While supporting the top portion of the **Side Panel**, pull the **Locking Latch** on the **Side Panel** downward, to release the **Side Panel** from the **Rack Frame**.



Locking Latch

2. Slowly tilt the top portion of the **Side Panel** away from the **Rack Frame**.
3. While supporting the weight of the **Side Panel**, pull the bottom of the **Side Panel** away from the **Rack Frame**.



Exposed Side Panels

Note: *The bottom of the* **Side Panel** *is hooked onto a lip on the* **Rack Frame**.

Installing the Side Panels

Note: *At least two people are required when removing or reinstalling the* **Side Panel** *from the* **Rack**.


1. While supporting the weight of the **Side Panel** align the bottom **Side Panel Lip** with the lip on the **Rack Frame**.
2. Slide the bottom **Side Panel Lip** into the lip on the **Rack Frame**.
3. Push the top of the **Side Panel** into the **Rack Frame** until you hear it click (lock) into place.

Removing the Roof Panel

The **Roof Panel** can be removed in order to run cabling.

Note: *At least two people are required when removing or reinstalling the* **Roof Panel** *from the* **Rack***.*

1. While pulling the two **Locking Pins** (located at the rear of the **Roof Panel**) push the **Roof Panel** up, to release the back portion of the **Roof Panel** from the **Rack Frame**.



Locking Pins

2. While supporting the weight of the **Roof Panel**, slide the two **Locking Tabs** (located at the front of the **Roof Panel**) out from the slots on the **Rack Frame**.
3. Carefully lift the **Roof Panel** out of the **Rack Frame**.

Grounding the Rack

1. Insert an **M6 Screw** through the grounding point on the **Grounding Wire** (sold separately) and into the **Ground Hole**, located on the bottom of the interior door frame (front and rear door frames).
2. Run the **Grounding Wire** under the **Rack Frame** to prevent obstructing the **Rack Door** from closing.
3. Connect the **Grounding Wire** to an earth-ground connection.


Adjusting the Vertical Mounting Rails or Cable Management Rails

The **Mounting Rail Depth** can be adjusted from 180 mm (7") to 893 mm (35").

> ***Note:*** *Follow the steps below to adjust the depth of the* **Cable Management Rails***.*

1. Each **Mounting Rail** has two **M6 Screws** and two **Cage Nuts** securing the **Mounting Rail** to two **Depth Adjustment Rails**. One **M6 Screw** and **Cage Nut** is located at the top and one is located at the bottom of the **Mounting Rail**.

2. Using a **Phillips Head Screwdriver**, remove the two **M6 Screws** from the **Cage Nuts** on the **Mounting Rail**.
3. Using a **Cage Nut Tool**, remove the two **Cage Nuts**.



Remove the two M6 Screws

4. Slide the **Mounting Rail** along the **Depth Adjustment Rails** until you have reached the desired mounting depth.



Mounting Rail

Notes: *The distance between each of the* **Mounting Rail Adjustment Holes** *is 1/4 inch.*

5. Using a **Cage Nut Tool** or your fingers, insert the two **Cage Nuts** through the **Mounting Rail** and into the **Depth Adjustment Rail**.


6. Insert the **M6 Screws** through the **Mounting Rail** and into the **Depth Adjustment Rails**. Use a **Phillips Head Screwdriver** to tighten the **M6 Screws**.

Baying Multiple Racks Together

Use the **Baying Brackets**, to connect or bay the **Rack** to multiple racks. There are four **Baying Brackets** two upper and two lower, located on the **Rack's Inner Door Frame**. Depending on the side of the **Rack** you are trying to bay to another rack you may need to remove the front door in order to access the **Baying Brackets** (e.g. baying to the side of the **Rack** where the door hinges are located).

1. Align the racks side by side with the rack's front doors facing forward.
2. Open the **Rack's Front Door** allowing you access to the inner door frame where the **Baying Brackets** are located.

3. Move the racks close enough so that the **Baying Brackets** when extended can align with the other rack's **Baying Screw Holes**.



Baying Bracket

Note: *The adjoining rack may have a* **Baying Bracket Screw** *already installed in the* **Baying Screw Hole**.

4. Using a **Phillips Head Screwdriver**, loosen the B**aying Bracket Screw** holding the **Baying Bracket** in place.
5. Turn the **Baying Bracket** enough to align the **Baying Bracket** with the **Baying Screw Hole**.
6. Insert an **M6 Screw**, through the **Baying Bracket** and into the adjoining rack. Use a **Phillips Head Screwdriver** to tighten the **M6 Screw**.
7. Retighten the **Baying Bracket Screw** that was loosened in step 4.

Technical Support

StarTech.com's lifetime technical support is an integral part of our commitment to provide industry-leading solutions. If you ever need help with your product, visit www.startech.com/support and access our comprehensive selection of online tools, documentation, and downloads.

For the latest drivers/software, please visit www.startech.com/downloads

Warranty Information

This product is backed by a five-year warranty.


StarTech.com warrants its products against defects in materials and workmanship for the periods noted, following the initial date of purchase. During this period, the products may be returned for repair, or replacement with equivalent products at our discretion. The warranty covers parts and labor costs only.

StarTech.com does not warrant its products from defects or damages arising from misuse, abuse, alteration, or normal wear and tear.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product.

Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



StarTech.com
Hard-to-find made easy®

Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.

Reviews

Share your experiences using StarTech.com products, including product applications and setup, what you love about the products, and areas for improvement.

StarTech.com Ltd.
45 Artisans Crescent
London, Ontario
N5V 5E9
Canada

StarTech.com LLP
4490 South Hamilton Road
Groveport, Ohio
43125
U.S.A.

StarTech.com Ltd.
Unit B, Pinnacle 15
Gowerton Road
Brackmills,
Northampton
NN4 7BW
United Kingdom

StarTech.com Ltd.
Siriusdreef 17-27
2132 WT
Hoofddorp
The Netherlands

FR: fr.startech.com
DE: de.startech.com
ES: es.startech.com
NL: nl.startech.com
IT: it.startech.com
JP: jp.startech.com

To view manuals, videos, drivers, downloads, technical drawings, and more visit www.startech.com/support