

2104 : ZR 42 6-40 mm plastic pipe cutter



The + product :

Soft Touch® non-slip knob, fast action adjustment.

Quick, tool-less wheel change.

4 guide rollers to prevent wheel tracking.

Description

Max thickness: 4 mm.


For pipes in plastic, composite materials and multilayer.

Precise cutting from Ø 6 to Ø 40 mm according to the type of tube.

1 spare wheel.

Retractable rotating reamer with interchangeable blades.

Grooved rollers for cutting tight up against flanges.



References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210489	6 - 40	1/4 - 1.1/2	187	76	4	0,520

