

M12 PCG/600A-201B

M12™ SUB COMPACT CAULK GUN WITH 600 ML TUBE

Up to 1780 N of force

REDLINK™ overload protection electronics in tool and battery pack deliver best in class system durability

Optimised performance with all construction adhesives and cool temperatures

Anti-drip feature prevents unwanted dripping when trigger is released

Dial control with 6 speed settings allows for maximum bead control

Large robust plunger design ensures constant flow, reduces blow back and expels all sealant from cartridge

Individual battery cell monitoring optimises tool run time and ensures long term pack durability

Fuel gauge displays remaining charge

REDLITHIUM™ battery pack provides superior pack construction, electronics and fade-free performance to deliver more run time and more work over pack life

Flexible battery system: works with all MILWAUKEE® M12™ batteries



REDLITHIUM™



Max. pushing force (N)	1,780
Speed settings	6
Standard equipment	600 ml alum. tube
Weight with battery pack (EPTA) (kg)	1.9 (M12 B2)
Kit included	1 x M12 B2 Battery pack, C12 C Charger, Tool bag
Article Number	4933448764