



PRODUCT-DETAILS

M20M12M

THEAD REDUCER BRASS M20/M12 ROUND



General Information	
Extended Product Type:	M20M12M
Product ID:	7TAA292550R0048
EAN:	7630030248733
Catalog Description:	THEAD REDUCER BRASS M20/M12 ROUND
Long Description:	MR Reducer, Brass, Metric Thread, Standard - Thread Inside Metric M12x1.5, Thread Outside Metric M20x1.5
Display Name:	M20M12M

Additional Information	
Product Main Type:	PMA Flexible Cable Protection
Application:	For Reduction of an Existing Thread
Product Type:	Conduit Reducer with Round Form

Ordering

EAN:	7630030248733
UPC:	786209960580

Technical

Number of Batteries:	0
Color:	Metallic
Material:	Nickel Plated Brass
Size:	M20 to M12

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	100 EA
Package Level 1 EAN:	7630030248733
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	M20M12M
Instructions and Manuals:	M20M12M
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC000938 - Enlargement/reducing ring
ETIM 9:	EC000938 - Enlargement/reducing ring
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

