

Features

- Many applications
- Mini design
- ABS V0

RS PRO Foot Switches

RS Stock No.: 0606330



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

This product are plastic foot switches in mini design that besides their robust form and technical versatility are specially convincing for their functionality and ergonomic design. They can be applied on foot switch operated machines such as: shearing machines, spinning lathers, machine tools, wrapping machines, riveting presses, etc.

General Specifications

Contact Configuration	Contact (1NO+1NC changeover)
Switch Operation	Snap contact
Case Material	Plastic
Switch Environment	Light Duty
Output Type	Analogue
Guard Cover	Yes
Standards Met	IEC 1058-1 / EN 61058-6
Colour	Grey
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	Faston
Accessory Type	Actuator
For Use With	Mechanical operated switch
Mechanical Durability	Mechanical 10000000 Cycles Electrical 100000 Cycles

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Voltage Rating (DC)	250V
Contact Current Rating	3A at 250V ac 0.06A at 230V dc
Operating Frequency	3600operations/hour max. 50-60Hz
Contact Resistance	30mΩ
Overvoltage Category	Class II

Mechanical Specifications

Length	127
Height	35
Dimensions	127x75x35
Width	75

Operation Environment Specifications

Operating Temperature	-25°C to 70°C
-----------------------	---------------

Protection Category

IP Rating	IP40
-----------	------

Approvals

Compliance/Certifications	CE
---------------------------	----