


FASCETTE A VITE A BANDA PIENA

Fascette a vite standard - Banda di
9 mm



Materiale

Acciaio

Codice	Ø min/max (mm)	Larghezza della banda	Peso netto (Kg)	Dim. A (mm)	Dim. B (mm)
PBS9 814	8 / 14	9	0,012	20	0.8
PBS9 1117	11 / 17	9	0,012	20	0.8
PBS9 1320	13 / 20	9	0,012	20	0.8
PBS9 1524	15 / 24	9	0,013	24	0.8
PBS9 1928	19 / 28	9	0,015	24	0.8
PBS9 2232	22 / 32	9	0,016	24	0.8
PBS9 2638	26 / 38	9	0,018	24	0.8
PBS9 3244	32 / 44	9	0,022	29	0.8
PBS9 3850	38 / 50	9	0,023	29	0.8
PBS9 4456	44 / 56	9	0,0235	29	0.8
PBS9 5065	50 / 65	9	0,026	32	0.8