



MILWAUKEE TOOL

Milwaukee Electric Tool Corporation
BROOKFIELD, WI 53005
USA
Tel: +1 (262) 781-3600 • Fax: +1 (262) 790-6333

Milwaukee Asia Office
29/F, Tower 2, Kowloon Commerce Centre,
51 Kwai Cheong Road, Kwai Chung, Hong Kong
Tel: +852-2492-2181 • Fax: +852-2490-4778

Distributed by:


All data incl. service and warranty conditions as well as product range are subject to change without notice.
Pictures not binding. No liability for printing errors or mistakes. © 2021 Milwaukee Electric Tool Corporation.
All trademarks are owned by Techtronic Cordless GP unless otherwise stated.

www.milwaukeetool.asia

Milwaukee™

M18 FUEL™


DRIVEN TO OUTPERFORM.™



POWERSTATE™
BRUSHLESS MOTOR



REDLINK PLUS™
INTELLIGENCE



REDLITHIUM™-ION
BATTERY PACK

M18 FSAGV

M18 FUEL
100MM / 125MM
BRAKING
VARIABLE SPEED
GRINDERS

GENERATES
CORDED
POWER

INCREASED
CONTROL

RAPIDSTOP
BRAKE



DRIVEN TO OUTPERFORM.

M18 FUEL is engineered for the most demanding tradesmen in the world. Delivering unrivaled performance in a compact structure, all M18 FUEL products feature three MILWAUKEE exclusive innovations - the POWERSTATE Brushless Motor, REDLITHIUM-ION Battery Pack and REDLINK PLUS Intelligence Hardware and Software - that deliver unmatched power, run-time and durability.

M18 FUEL

RAPIDSTOP BRAKE

Stops accessory in under 2 seconds

VIBRATION DAMPENING SIDE HANDLE

Provides safety during use with additional comfort

TOOL-FREE GUARD ADJUSTMENT

Faster guard installation and adjustments for less down time

TOOL-FREE ACCESSORY CHANGES

Pre-installed fixtec nut technology allows for tool-free accessory changes while remaining fully compatible with the most common accessories in the market



POWERSTATE BRUSHLESS MOTOR

Delivers corded power and 8,500 rpm to remove material faster and increase productivity

SPEED DIAL

5 Speed settings for more control in different applications

M18 REDLITHIUM-ION BATTERY

Fits all M18 tools

PADDLE SWITCH / SLIDE SWITCH

Slide or paddle switch design to fit users preferences

TYPE 27 GUARD

T27 guard for use when completing grinding applications

M18 FUEL 100MM / 125MM VARIABLE SPEED BRAKING GRINDERS

GENERATES CORDED POWER



- POWERSTATE Brushless Motor spins at 8,500 RPM, providing power of comparable corded tools

INCREASED CONTROL



- Variable speed control for applications that require lower RPM grinding
 - 3500 -8500 RPM
 - 5 Speed Settings

RAPIDSTOP BRAKE



- Stops all accessories in under 2 seconds
- Kickback brake protects against bind up situations and reduces risk of kickback



MODELS

- M18 FSAGV100XB**
M18 FUEL 100MM BRAKING VARIABLE SPEED ANGLE GRINDER SLIDE SWITCH
- M18 FSAGV125XB**
M18 FUEL 125MM BRAKING VARIABLE SPEED ANGLE GRINDER SLIDE SWITCH
- M18 FSAGV100XPDB**
M18 FUEL 100MM BRAKING VARIABLE SPEED ANGLE GRINDER PADDLE SWITCH
- M18 FSAGV125XPDB**
M18 FUEL 125MM BRAKING VARIABLE SPEED ANGLE GRINDER PADDLE SWITCH

SPECIFICATIONS

DESCRIPTION			SPECIFICATIONS		
			M18 FSAGV100XB M18 FSAGV100XPDB	M18 FSAGV125XB M18 FSAGV125XPDB	
RPM			3,500 - 8,500		
Grinding Disc Diameter			100 mm	125 mm	
Spindle Thread			M10	M14	
Grinding Disc Hole Diameter			16 mm	22.2 mm	

DESCRIPTION			SPECIFICATIONS		
			M18 FSAGV100XB M18 FSAGV100XPDB	M18 FSAGV125XB M18 FSAGV125XPDB	
Speed Settings			5		
Tool-free Guard Change			Yes		
Overload Protection			Yes		
Weight (w/M18 B5)			2.6 kg	2.7 kg	