

Dust Extractor LXT®

DVC155L

18V X 2 • 110 mbar • 15 l • L

Wet/dry dust extractor for cleaning

A versatile wet/dry dust extractor that runs on two 18V LXT® batteries. Matches filter class 'L'. Run time with 6.0 Ah batteries is about 40 min.



Technical specifications

Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
Brushless Motor	✓
Air volume	2,1 m³/min
Max. sealed suction	110 mbar
Vacuum hose length	1,7 m
Vacuum hose diameter	32 mm
Tank Capacity for Dust	15 L
Tank Capacity for Liquids	12 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	2,5 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Dust Class	L
Tool weight with battery	7,2 - 7,9 kg
Product Dimensions (L x W x H):	366 x 334 x 421 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-)	Li-ion

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Low noise level for pleasant work.
- Approved for Dust Class L in accordance with the EU standard
- Battery protection system automatically shuts off power when the battery level is low
- Variable suction power control by dial

Link to product - www.makita.uk.com



Related products

Optional AC

140G19-0

Aluminium telescopic pipe with pipe

140H94-2

Soft Brush 360 Complete Set, Blue

191G86-8

Nozzle assembly set

195432-5

Poly Bag Set, 10 pcs

195547-8

Adapter 22 / 25 mm

197901-2

Flexible rubber nozzle

198919-6

Corner nozzle white

199041-2

Seat nozzle set

422437-5

Rubber Crevice Nozzel 330 x Ø35



140G26-3

Bent Pipe Assembly With Pipe Lock



140H95-0

Seat Nozzle, Ø32 Mm



191M30-1

Brush Nozzle



195433-3

Hose Ø 28 mm x 3,5 m



197166-6

Powder filter set



198532-0

Nozzle assembly 320 mm



199038-1

Seat Nozzle Set 175 mm



199493-7

Hose complete Ø 32 mm x 1700 mm



Other

User manual

Parts drawing