

SAUTER AC 22R



Standard Screw Tension Clamp for tension and rupture tests



Category

Brand	Sauter
Product category	Clamp
Product group	Screw tension clamp

Construction

Material	steel
Mounting - force dissipation	Threaded hole M6
Maximum clamp width	30 mm
Clamping width	3 mm
Tensile/compressive force [Max]	500 N

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	150×100×10 mm
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,15 kg
Shipping weight	0,125 kg
Shipping volume weight	0,1 kg

Product information

GTIN/EAN number	4045761122826
Trade number	90278990
REACH classification	no prohibited substances

Pictograms

STANDARD

