



Short elbow hexagonal keys in mm

62-...Cles_en_MM

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-10-13 08:41:20





DESCRIPTION

Short elbow hexagonal keys in mm

steel with chrome vanadium

For hexagon socket screws

burnish presentation

STANDARDS / DIRECTIVES

NF ISO 2936, ISO 2936

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France


RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-10-13 08:41:20



SPECIFIC DATA



Sales reference	L (mm)	Weight (g)	H (mm)	A (mm)	Guarantee
62-8	107	60	37	8	O
62-7	102	40	35	7	O
62-14	155	265	55	14	O
62-0,9	33	1	11	0.9	O
62-5	85	18	28	5	O
62-13	149	225	52	13	O
62-1,3	43	2	11	1.3	O
62-2,5	59	3	18	2.5	O
62-10	122	107	40	10	O
62-12	138	170	46	12	O
62-2	52	2	16	2	O
62-3	65	5	19.5	3	O
62-11	130	135	42	11	O

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-10-13 08:41:20



62-4	75	11	25	4	O
62-19	199	615	69	19	O
62-9	114	80	39	9	O
62-1,5	48	2	14	1.5	O
62-0,7	34	1	8	0.7	O
62-6	94	31	32	6	O
62-17	175	442	60	17	O

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-10-13 08:41:20

