



PRODUCT-DETAILS

BVNV-M200
COND FTNG STR M20 NW10 IP68 CSA BLK



General Information	
Extended Product Type:	BVNV-M200
Product ID:	7TAA292150R0272
EAN:	7630030212055
Catalog Description:	COND FTNG STR M20 NW10 IP68 CSA BLK
Long Description:	PMAFIX Straight Black Connector, Material - Polyamide 6, Thread Size M20x1.5, Conduit Size NW - 10
Display Name:	BVNV-M200

Additional Information	
Product Main Type:	PMA Flexible Cable Protection
Application:	For Cable Protection Systems In a Wide Range of Applications
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030212055
UPC:	786209952325

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide 6
Size:	NW10 , M20 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

Container Information

Package Level 1 Units:	50 EA
Package Level 1 EAN:	7630030212055
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	BVNV-M200
Instructions and Manuals:	BVNV-M200
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

