


**NATR5**

Galet de roulement

Yoke type track rollers NATR..., single row needle roller bearings with particularly thick-walled outer ring, needle roller and cage assembly and an inner ring, axial guidance of outer ring is provided by the contact washers, gap seals on both sides

Information technique



Votre alternative produit actuelle

|                             |      |                                         |
|-----------------------------|------|-----------------------------------------|
| joint                       | SPSP | Gap seal on both sides                  |
| profile bague extérieure    | R500 | Diamètre extérieur sphérique (Standard) |
| dispositif de lubrification | IR   | Via inner ring                          |

dimensions principale & données de performance

|                     |              |                                                         |
|---------------------|--------------|---------------------------------------------------------|
| d                   | 5 mm         | Alésage                                                 |
| D                   | 16 mm        | Diamètre extérieur                                      |
| B                   | 12 mm        | Largeur, bague intérieure                               |
| C <sub>r w</sub>    | 3.200 N      | Charge dyn. de base, radiale                            |
| C <sub>0r w</sub>   | 3.450 N      | Charge stat. de base, radiale                           |
| C <sub>ur w</sub>   | 465 N        | Limite à la fatigue, radiale                            |
| n <sub>D G</sub>    | 14.000 1/min | Vitesse pour une lubrification à la graisse             |
| F <sub>0r per</sub> | 3.450 N      | Charge radiale statique admissible                      |
| F <sub>r per</sub>  | 3.450 N      | Charge radial dynamique admissible sur bague extérieure |
| ≈m                  | 15,1 g       | Poids                                                   |

Dimensions

|                  |         |                                        |
|------------------|---------|----------------------------------------|
| C                | 11 mm   | Largeur, bague extérieure              |
| d <sub>2</sub>   | 12,5 mm | Diamètre extérieur rondelle de butée   |
| r <sub>min</sub> | 0,15 mm | Dimension minimum de chanfrein         |
| R                | 500 mm  | Rayon bague extérieure profile externe |



### Caractéristiques

---



Effort radial



Lubrification à la graisse



lubrification à l'huile



Ouvert