

Modular Plug (4P4C)



Modular Plug (PCB44)

4 position 4 contact plug used on coiled handset leads and telephone headsets. Also known as RJ9, RJ10 or RJ22 connector

Features

- Suitable for flat cable
- UL listed
- Contact blades are suitable for solid and/or stranded wire from 24-26 AWG
- Shielded, customised logos and colours are available to order
- Also available for round cable (PGB44)

Specifications

- Net weight: 43g (bag of 50 including primary packaging)
- Dimensions: 100x70x15mm (bag of 50)
- Housing: Polycarbonate, UL94V
- Contacts: 15µ" / 0.38µm Gold plated over 100µ " / 2.54µm Nickel plate over Phosphor Bronze

