

Features

- **Energy Efficiency:**
RS PRO "A" Energy Rated at 210 lm/W GU10 lamps, delivering exceptional luminous efficacy for maximum energy savings.
- **Long Lifetime:**
Designed for durability with a 50,000-hour lifespan, reducing maintenance and replacement costs.
- **Environmental Impact:**
Better World Approved. Supports sustainability with a 95% reduction in annual CO₂ emissions compared to traditional lighting solutions.
- **Colour Performance:**
Meets IEC chromaticity standards (x, y coordinates) with no green light deviation, ensuring clean, accurate colour rendering.
- **3-year guarantee**

RS PRO 2.5W "A,, ENERGY RATED 210lm/W LED GU10 LAMP

Non-DIMMABLE -3000K

RS Stock No.: 0733494



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

LED Lamps

Product Description

RS PRO 2.5W "A" Rated LED GU10 Lamp delivers ultra-high efficiency at 210 lm/W with dimmable and non-dimmable options.

With a 50,000-hour lifespan and 95% lower CO₂ emissions, it's an eco-friendly choice. Precise colour accuracy meets IEC standards for clean, reliable lighting.

General Specifications

Luminosity	450lm
Light Source Luminosity	480lm
Efficiency	210lm/W
Operating Current	0.271A
Power Factor	>0.5
Colour Temperature	3000K
Beam Angle	100°
Dimmable	No
Energy Rating	A
Lifespan	50,000 Hours
Lamp Type	SMD LED
Warranty	3 Years

Electrical Specifications

Wattage	2.5W
Voltage Rating	220-240V

Mechanical Specifications

Length	53mm
Diameter	50mm
Depth	50mm

LED Lamps

Protection Category

IP Rating	IP20
-----------	------

Operation Environment Specifications

Operating Temperature	-20~45°C
-----------------------	----------

Approvals

Compliance/Certifications	LVD, EMC, RoHS
Standards Met	BS EN 60598-1