

KERN 366-89

KERN

Individual weight, OIML Class M3, 50 kg, Block, cast iron lacquered



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M3
Product family	366

Measuring System

Test weight - nominal value	50 kg
Test weight - volume uncertainty (cm ³)	595,12
Weight OIML class	M3
Conformity assessment possible	no
Test weight - volume (cm ³)	7042,2535
Permissible tolerance according to OIML (+/-)	25 g
OIML-compliant	✓
Test weight - Density [Min] (OIML)	1500
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction

Shape weight	Block
Dimensions weight (W×D×H)	310×155×192 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAKkS calibration	962-646
--------------------------------------	---------

Packing & Shipping

Delivery time	2 d
Dimensions packaging (W×D×H)	310×155×192 mm
Shipping method	Freight
Net weight approx.	50 kg
Gross weight approx.	50 kg
Shipping weight	50 kg
Shipping volume weight	1,8 kg

Product information

GTIN/EAN number	4045761012028
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

