

Hinge 8 Al FP4, light duty




REACH RoHS

Hinges Al, light duty are suitable for use with swing doors, flaps and lids constructed using profile frames or solid panels.

When fitting Hinges Al light in the 4 mm door gap between the door and the frame (designation "4"), the fastening screws are covered over when the door is closed, making them inaccessible.

Hinges Al, light duty are available as complete sets for all popular combinations of profiles and for combinations of profiles and panel elements.

FP4 hinges can be effectively protected from outside manipulation by using a self-locking nut on the screw in the panel element.



Scope of Delivery

2 hinge leaves, Al, anodized, natural
T-Slot Nut V 8 St M6, bright zinc-plated
Countersunk Screw DIN 7991-M6x14, bright zinc-plated
Hinge Al light, Pin Set D6
Notes on Use and Installation

Technical note

[0.0.488.96](#) Please click here for further information!

Properties	
Article number	0.0.488.96
Delivery unit	1 set
Weight	96.0 g
cleanroom suitability	Yes
Force max	500 N

Accessoires	
0.0.719.08	Clinch Nut M6x3.6
0.0.406.39	Key with T-Handle 4 A/F
0.0.650.50	Key Insert 4 A/F-1/4"