

KERN 326-12

KERN

Individual weight, OIML Class F1, 2 kg, Eco Shape, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	326

Measuring System

Test weight - nominal value	2 kg
Weight OIML class	F1
Permissible tolerance according to OIML (+/-)	10 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7390
Test weight - Density [Max] (OIML)	8730
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Eco Shape
Dimensions (Ø×H)	60×106 mm
Material	stainless steel polished
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-442
Article number for guaranteed plus-deviation	921-442

Packing & Shipping

Delivery time	1 d
---------------	-----

Dimensions packaging (W×D×H)	60×60×102 mm
Shipping method	Parcel service
Net weight approx.	2,0 kg
Gross weight approx.	2,0 kg
Shipping weight	2 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	347-120-400
Case - Aluminium article number	317-120-600
Case - Wood article number	317-120-100

Product information

GTIN/EAN number	4045761223646
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

