

## Compact magnetic cylinders - Series 32

Product code: 32M2A020A075

Datasheet creation date: 19/05/2026 11:32

Check the most updated document online [click here](#)




### TECHNICAL DATA

|                             |                                                     |
|-----------------------------|-----------------------------------------------------|
| <b>Series</b>               | 32                                                  |
| <b>Version</b>              | M=male rod thread                                   |
| <b>Operation</b>            | 2=double-acting                                     |
| <b>Materials</b>            | A = anodized aluminium body, end blocks and piston, |
| <b>Diameter (mm)</b>        | 20                                                  |
| <b>Construction</b>         | A = standard                                        |
| <b>Cylinder Stroke (mm)</b> | 75                                                  |
| <b>Seal options</b>         | = standard                                          |
| <b>Rod length (mm)</b>      | 0                                                   |
| <b>Rod lenght 2 (mm)</b>    | 0                                                   |
| <b>Certifications</b>       | = standard                                          |

## Compact magnetic cylinders - Series 32

Product code: 32M2A020A075



### DIMENSIONS

|          |      |
|----------|------|
| A (mm)   | 16   |
| AF (mm)  | 11   |
| BG (mm)  | 20.0 |
| G (mm)   | 10.9 |
| Ø (mm)   | 10   |
| Ø (mm)   | 9    |
| D4 (mm)  | 9    |
| D5 (mm)  | 6    |
| D6 (mm)  | 0    |
| D7       | M4   |
| D8 (mm)  | 4    |
| E (mm)   | 35.8 |
| EE       | M5   |
| H (mm)   | 8    |
| KF       | M6   |
| KK       | M8   |
| LA (mm)  | 5    |
| L4 (mm)  | 17   |
| PL (mm)  | 6.5  |
| RT       | M5   |
| SW1 (mm) | 8    |
| T2 (mm)  | 2    |
| T3 (mm)  | 0    |

|         |      |
|---------|------|
| TG (mm) | 22.0 |
| ZA (mm) | 36.8 |
| ZB (mm) | 42.5 |
| ZC (mm) | 48.2 |