

Category 6 Keystone Panel Mount Coupler (Shielded)



Category 6 Keystone Panel Mount Coupler Shielded (SACK3S, SACK3S-24)

Features

- Designed to fit US industry standard keystone mount outlets wall plates and patch panels
- RJ45 complies with FCC68
High performance data throughput, meets Category 6 data transfer rates
- Operating temperature: -40°C to +85°C
Jack insertion life > 750 mating cycles
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

Packaging:

- Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK3S-24 is available as a "bulk pack" of 24 pieces without individual bags.

Specifications

- Dimensions
SACK3S: 29.7 x 17 x 19.25 mm approx. **SACK3S-24:** 280 x 70 x 35mm approx.
- Materials:
Housing: Nickel plated zinc alloy
Contacts: 50µ"/ 1.27µm gold plating over nickel plated phosphor bronze
Earthing lug material: Stainless steel SUS304
- Weight:
SACK3S: 18g approx. **SACK3S-24:** 460g approx.

Commodity code: 85369010

EAN:




SACK3S: 5055386503961

SACK3S-24: 5055386504999

Country of Origin: China

ROHS Compliant

Code: SACK3S



ELECTRICAL:

Current Rating : 1.5A
 Dielectric Withstanding Voltage : 1000V/AC 60Hz
 Insulation Resistance : 500 MΩ MIN.
 Contact Resistance : 20 mΩ MAX.

MECHANICAL:

Durability: RJ45 With 750 Mating Cycles
 and RJ11 With 200 Mating Cycles
 Supporting Cable Diameter: 6~9mm
 Operating Temperature: -40°C to +85°C
 Storage Temperature: -40°C to +85°C

MATERIAL:

Dust cap: PP
 Ground Lug: SUS304
 Front cover: Zn alloy + Nickel Plated
 LATCH: PC 94VO
 Bottom cover: Zn alloy + Nickel Plated