

BW 2400 RSC24AXXL

mobile pedestal with 8 drawers, long version, equipped with anti-tip system and assortment of 1,061 tools

Main features:

- 1 drawer measuring 1,176x367 mm with full extension, mounted on telescopic ball bearing slides
- 7 drawers of 882x367 mm full-extension, mounted on telescopic ball bearing slides:
- 6 drawers height 70 mm
- 1 drawer height 140 mm

- Stainless steel-coated MDF worktop with holes for placing a 1599F/125 or 1599GI/125 vice (to be ordered separately) and 6 tool trays
- High-strength nylon fronts with integrated label holder
- Drawer tops protected by foam rubber mats
- Removable side compartment, mounted on telescopic ball bearing slides, with shelf and lock
- Four Ø 150 mm wheels of which 2 fixed and 2 swivel with brake
- 3 security locks
- Integrated paper holder
- Integrated paper holder
- Static load capacity: 1,100 kg

- Possibility of inserting
- up to 8 soft EVA or thermoformed rigid ABS trays in the 1,176x367 mm drawer
- up to 6 soft EVA or thermoformed rigid ABS trays in the 882x367 mm drawer



art.			
024006381	BW 2400 RSC24AXXL-O		Orange
024006387	BW 2400 RSC24AXXL-A		Anthracite grey
024006383	BW 2400 RSC24AXXL-R		Red

n. 22 42: 6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-27-30-32 mm

n. 11 **BW 55:** Double open end wrenches
6x7-8x9-10x11-12x13-14x15-16x17-18x19-20x22-21x23-24x27-30x32 mm

n. 7 **BW 94:** Flare nut open ring wrenches
8x10-10x11-11x13-12x14-17x19-19x22-22x24 mm

n. 12 **BW 141:** Ratcheting combination wrenches
8-9-10-11-12-13-14-15-16-17-18-19 mm

n. 3 **BW 30:** Drift punches Ø 2-3-4 mm

n. 6 **BW 31:** Pin punches Ø 2-3-4-5-6-8 mm

n. 1 **BW 32:** Centre punches Ø 4 mm

n. 1 **BW 32AU:** Automatic centre punch

n. 2 **BW 34:** Flat chisels 150-175 mm

n. 1 **BW 36:** Cape chisels 150 mm

n. 1 **1032:** ♂ 19÷60 mm

n. 1 **1034:** ♂ 19÷60 mm

n. 1 **1036:** ♀ 19÷60 mm

n. 1 **1038:** ♀ 19÷60 mm

n. 1 **BW 1048:** Slip joint pliers, boxed joints 250 mm

n. 1 **BW 1047:** Slip joint pliers, push button adjustment 240 mm

n. 2 **BW 1052:** Adjustable self-locking pliers, concave jaws 190-240 mm

n. 1 **BW 1082BM:** Diagonal cutting nippers 160 mm

n. 1 **BW 1150BM:** Heavy-duty combination pliers 180 mm

n. 1 **BW 1166BM:** Extra-long needle knurled nose pliers 200 mm

n. 1 **BW 1168BM:** Extra-long bent needle knurled nose pliers 200 mm

n. 1 **BW 1370:** Engineer's hammers 300 g

n. 1 **BW 1380:** Lump hammer 1000 g

n. 1 **BW 1390:** Soft face hammer, plastic faces Ø 35 mm

n. 1 **BW 990:** Straight thin knurled point spring tweezers 130 mm

n. 1 **BW 991:** Bent thin knurled point spring tweezers 130 mm

n. 1 **BW 993:** Pin spring tweezers, made from stainless steel 145 mm

n. 1 **BW 994:** Straight large point spring tweezers 150 mm

n. 10 **BW 720L:** Impact sockets, long series, 1/2" ♂ ♀

10-12-13-15-17-19-21-24-27-30- mm

n. 1 **BW 720/21:** Machine extension - 1/2" 125 mm

