

KERN 356-78

KERN

Individual weight, OIML Class M2, 20 kg, Block Eco, cast iron lacquered



Dimensions packaging (W×D×H)	230×115×139 mm
Shipping method	Parcel service
Net weight approx.	20 kg
Gross weight approx.	20 kg
Shipping weight	20 kg
Shipping volume weight	0,7 kg

Optional cases

Case - Aluminium article number	346-080-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761241800
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - nominal value	20 kg
Test weight - volume uncertainty (cm³)	238,048
Weight OIML class	M2
Test weight - volume (cm³)	2816,9014
Permissible tolerance according to OIML (+/-)	3 g
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300
Test weight - Density (kg/m³)	7100
Test weight - Density uncertainty (kg/m³)	600

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	230×115×139 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkks calibration	962-645
--------------------------------------	---------

Packing & Shipping

Delivery time	1 d
---------------	-----