

20A DP Switches



Description

Metalclad offers a tough and impact resistant range of accessories with a durable finish and protective coating.

Each product is supplied with a surface mount metalclad back box and in its own polybag, protecting it up to the point of installation.

Features

- Durable and tough finish with protective coating
- Supplied complete with surface mounting box with knockouts
- Neon and flex outlet options
- Captive and backed out terminals
- Terminals have clearly embossed markings
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- Neon leads enclosed
- Recessed earth bar
- Angled terminals to aid installation
- 2 earth terminals
- 25-year guarantee

Technical Specification

Voltage rating	250Vac
Current Rating	20A
Contact gap	3mm

No user serviceable parts

Standards

- BS EN 60669-1

Range

20A DP Switch Neon	VM1391
20A DP Switch Neon Flex Outlet	VM1393

Back Boxes

All knockouts are 20mm diameter.

	Sides	Back
1g	5	1

Terminal Capacity

	2.5mm ²	4mm ²	6mm ²	10mm ²
L & N	4	2	2	1