



Lighting **excellence**



@4liteuk



@4liteuk



@4lite




@4liteuk

T8 LED Tube CCT

T8 LED Tube CCT 1500mm

Code: 4L3/3002

Application Industrial



Product Features

- Energy-efficient T8 LED glass tube
- Adjustable wattage, allowing selection between high or low output
- Easy to install and the perfect replacement for traditional fluorescent T8 tubes
- Instant light output
- Suitable for residential and commercial applications
- 3 CCT Selectable between 3000K, 4000K & 6500K
- High efficacy up to 140 lm/w
- 5 year warranty

Technical Information

Wattage	12W / 22W
Lumens Delivered	1700lm / 3100lm (4000K)
Lm/W	140lm/w / 150lm/w
Beam Angle	360
CRI	80
CCT	3000/4000K/6500
Input	220-240V
Operating Temp	-20°C to 45°C
SDCM	6
Product Weight without Packaging	0.247 kg

Technical Information

Light Source	T8
IP Rating	IP20
Class Protection	2
Internal / External	Internal
Lumen Depreciation	L70 B50 25,000h
Warranty (Years)	5
CE Mark	Yes