


Category 6/6A Shielded Modular Plug (8P8C)



(PXcat6S8XL2)

(PXcat6S4)

Features

We are pleased to offer high performance shielded connectors suitable for rapid termination of Category 6 and Category 6A patch cables. No soldering is required and the plugs can be terminated well in the field or on an automated production line.

PXCAT6S8XL2

- Contact blades are suitable for stranded or solid wire from 22-26 AWG. cores up to 1.15mm O.D.
- 2 part (plus foil) plug with large entry for large outer diameter cable (easily accommodates 7mm O.D.).
- Compatible SR boot also available in black or white (PS2bk8 + PS2wh8).

PXCAT6S4

- Contact blades are suitable for stranded or solid wire from 22-26 AWG. cores up to 1.02mm O.D.
- 3 part (plus foil) plug with extra cross insert separators and 1/3/7 pattern low insert for high performance.
- Suitable for use with flush or overboot style SR.

Specifications

- Suitable for round Category 6/6A FTP cable. Enables reliable termination to Category 6/6A component level patch lead standard.
- UL listed.

- Housing: Polycarbonate, UL94V.
- Shielding: Nickel-plated copper.
- Contacts: 50μ"/1.27μm Gold plated over 100μ"/2.54μm Nickel plate over Phosphor Bronze.
- Foil wrap.

Commodity code: 82032090


EAN:









PXcat6S8XL2#10 5055386504968

PXcat6S8XL2#50 5055386500113

PXcat6S4 5055386514554

Country of Origin: China





FOR WIRE OD:1.05-1.15mm.
CABLE OD:7.0mm MAX.

⑤	COPPER FOIL	COPPER	35X10mm	1	ZFCUDBXXX
④	Shielded	Cu	CAT6 8P	1	ZPG88XXXX-08
③	INSERT	PC	8P	1	PG88XgNOBXSO-IH1
②	HOUSING	PC	8P 5,1P	1	PH88XgNOBXSO-G
①	Contact Pin	Cu	High low PIN	4	GP16XXX
				4	GP13XXX
					Drøwing









APPD.		P/N.	PG88XgNOBXSO-G
CHKD.		FILE	PG88XgNOBXSO.DWG
DR.		TITLE	Suitable for cat 6 stranded cable wire OD:1.05-1.15

TUK Ltd	SCALE	SIZE
Cat 6 FTP Plug for large cores & OD	/	A4
PXCAT6S8XL2	UNIT	REV.
	MM	A0

REV.	DESCRIPTION	DATE	ENG.	APPROVAL
1				



ROHS COMPLIANT



Double CAT.6(1'3'7' Low) Insert

Cross Insert

8P8C 5.1F "T" mark Double 137' Low CAT6
Insert add cross insert Shielded PLUG

⑥	Metal Foil	Aluminium	35X8mm	1	
⑤	Shielded	Cu	—————	1	
④	Cross insert	PC	8P	1	
③	Insert	PC	137 Low Insert	1	
②	Housing	PC	8P&C	1	
①	Contact Pin	Cu	Big Angle	3	
No.	Name	Material	Specification	Qty'	Drawing

APPD.	P/N.	PXCAT6S4	
CHKD.	FILE		
DR.	TITLE		

TUK LTD		SCALE	/	SIZE	A4
UNIT	MM	REV.			

TUK LTD

Tuk Ltd, Unit 4, Wimbledon stadium Business Centre, Riverside Road, London SW17 0BA
Tel: 020 8946 6688 Fax: 020 8879 7410 Email: sales@tuk.co.uk Website: www.tuk.co.uk