

Features

- Compact industrial lockout padlock designed for reliable safety applications.
- Reinforced non-conductive ABS body for enhanced durability and protection.
- 6-pin high-security cylinder for improved locking precision and security.
- Stainless steel corrosion-resistant shackle for long-lasting performance.
- Key retaining safety mechanism to prevent key removal before locking.
- Supplied with 1 unique coded brass key for controlled access.
- Front "DANGER" label & rear ID label for clear safety identification.
- Suitable for indoor & outdoor use across various industrial environments.

RS PRO Lockout Safety Padlock with Stainless Steel Shackle - Green

RS Stock No.: 0813774



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- **Compact & High-Security Design** - Developed specifically for industrial users requiring reliable and space-efficient lockout solutions.
- **6-Pin Precision Cylinder** - Provides enhanced security with a high number of key differences, reducing the risk of duplicate keys.
- **Key Retaining Mechanism** - Prevents key removal until the padlock is fully locked, ensuring proper lockout procedures.
- **Reinforced ABS Body** - Durable and ergonomically designed with carved ribs for improved grip, easy handling and long service life.
- **Non-Conductive & non-sparking** - Suitable for electrical and hazardous environments.
- **Chemical & Corrosion Resistance** - Designed to withstand harsh industrial conditions, including exposure to chemicals and moisture.
- **Stainless Steel Shackle** - Provides superior corrosion resistance, ideal for Marine environments, chemical plants and outdoor applications.
- **Safety Labelling System** - DANGER label on the front & Personnel identification label on the back.
- **Individually Coded Keys** - Each padlock is supplied with a unique coded brass key for maximum security.

General Specifications


Type	Lockout Safety Padlock
Material	ABS body with SS shackle
Colour	Green
Package	Single-wall box

Mechanical Specifications

Shackle Height (A)	42mm
Shackle Diameter (B)	6mm
Body Height (C)	45mm
Body Width (D)	43mm
Body Depth (E)	20mm
Internal Height (F)	38mm
Weight	92 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 110°C
-----------------------	----------------



Dimension in mm	
Shackle Height (A)	42
Shackle Dia (B)	6
Body Height (C)	45
Body Width (D)	43
Body Depth (E)	20
Internal Height (F)	38