


2104 : ZR 42 Copper Tube Cutter 6-42 mm



The + product :

Soft Touch® non-slip knob, fast action adjustment.

Quick, tool-less wheel change.

4 guide rollers to prevent wheel tracking.

Description

Max thickness: 2 mm.

Precise cutting from Ø 6 to Ø 42 mm according to the type of tube.
1 spare wheel.

Retractable rotating reamer with interchangeable blades.

Grooved rollers for cutting tight up against flanges.

Colour-coded end cap according to the material to be cut.

References

Sku	A mm	A " OD	L mm	H mm	E maxi mm	kg
210445	6 - 42	1/4 - 1.5/8	187	76	2	0,515

