

HRP-POA 63G

Levelling castor, with integrated truck lock and top plate fitting, nylon wheel

EAN 4047526117580

ID 757020

Customs tariff number 83022000

Bracket: HRP series

- die-cast aluminium, powder-coated, colour ivory
- sealed ball bearing in the swivel head
- steel top plate
- truck lock made of hard rubber
- height adjustment using wrench or integrated adjustment wheel
- steel parts zinc-plated, blue-passivated, Cr6-free

Wheel: POA series

- high-quality nylon 6, impact resistant, hardness 70 Shore D, colour black

Other features:

- Load capacity determined under the following conditions:
 - speed: max. 1 km/h
 - temperature: +15 °C to +30 °C
 - hardness, horizontal tread without obstacles
 - route: A cooling off period of 15 minutes is required after a maximum of 50 m

Technical data:

Wheel Ø (D)		63 mm
Wheel width		30 mm
Load capacity at 1 km/h		500 kg
Static load capacity when stable and locked		600 kg
Bearing type		plain bore
Total height (H)		104 mm
Max. total height (h)		117 mm
Max foot floor clearance (T3)		11 mm
Mounting type		top plate
Plate size		90 x 90 mm
Bolt hole spacing		70 x 70 mm
Bolt hole Ø		9 mm
Adjustment range (T4)		13 mm
Offset (F)		46 mm
Temperature resistance min		-10 °C
Temperature resistance max		80 °C
Tread and tyre hardness		70 Shore D
Unit weight		1.4 kg
Non-marking		✓
Non-staining		✓
Antistatic		✗



Tread and tyre hardness

 70 Shore D

Rolling resistance


 excellent

Wear resistance

 good

Operating noise / floor surface preservation

 satisfactory



Electrically conductive		×
Corrosion-resistant		×
Heat-resistant		×
Suitable for autoclaves		×
Suitable for machine washing		×