


2533 : Manual Axial Crimping Tool for PEX series 5

The + product :

Quick tool change.
Effort reducing mechanism. **Quick crimping.**
Capacity from Ø 12 to 32 mm.

Description

Ergonomic polypropylene handles.
Reset trigger.
Removable, reversible adaptor to suit the different couplings on the market.
Rapid feed system.
6 reducers and 1 adaptor are available for performing Ø 12, 16, 20, 25 and 32 mm crimps on the following couplings: union, T, 90° elbow, captive or free-turning captive nut.



More Information

Capacity	Ø 12 to 32 mm.
Supplied with	In a plastic case.

References

Sku	Description	kg
253300	Ø 16, 20, 25 and 32	3,260

Sku	Description	kg
253302	Ø 12, 16, 20 and 32	3,270
253303	Ø 12, 16, 20, 25, and 32	3,310
253380	Machine only	1,250
253381	Case	0,840

