


RSTO8-TV

Galet de roulement

Yoke type track rollers RSTO..., single row needle roller bearings with particularly thick-walled outer ring, needle roller and cage assembly, without inner ring, without axial guidance of the outer ring, open, inner ring, outer ring and needle roller and cage assembly can be mounted separately

Information technique



Votre alternative produit actuelle

joint	Sans	
profile bague extérieure	R500	Diamètre extérieur sphérique (Standard)
Cage	TV	Cage plastique en PA66

dimensions principale & données de performance

D	24 mm	Diamètre extérieur
F _w	12 mm	Diamètre sous rouleaux
C	9,8 mm	Largeur, bague extérieure
C _{r w}	4.200 N	Charge dyn. de base, radiale
C _{0r w}	5.600 N	Charge stat. de base, radiale
C _{ur w}	800 N	Limite à la fatigue, radiale
n _{D G}	8.000 1/min	Vitesse pour une lubrification à la graisse
≈m	23 g	Poids

Dimensions

E	15 mm	Diamètre de piste bague extérieure
r _{min}	0,3 mm	Dimension minimum de chanfrein
R	500 mm	Rayon bague extérieure profile externe



Caractéristiques



Effort radial



Lubrification à la graisse



lubrification à l'huile



Ouvert