

M18 ONEFIW2FC12-0X

M18 FUEL™ ONE-KEY™ TORQUE-SENSE™ 1/2" CONTROLLED SOLAR COMPACT IMPACT WRENCH WITH FRICTION RING

TORQUE-SENSE™ torque control delivers greater torque repeatability than blow counting impact wrenches by utilising proprietary sensors and machine learning algorithms to overcome common job site variability. Customisable torque ranges from 67 to 203 Nm

TORQUE-SENSE™ error reduction feature set includes low battery shut-off, double hit prevention, early trigger release detection, F/R direction lock, programmable LED colours, and torque recheck timer

Elimination of the 2-step installation process and a simplified setup process via ONE-KEY™ ensure 3X faster installation

LED light indicator shows OK/ NOK installation. Every trigger pull is recorded and can be downloaded in form of customisable tool reports

Over the air update capable for future mode improvements

Reinforced battery connection providing improved durability and battery retention over life

Tri-LEDs deliver shadow-less high definition lighting to increase workspace visibility

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	0 - 1,125/ 0 - 1,525/ 0 - 1,850/ 0 - 2,325
Impact rate (ipm)	0 - 1,650/ 0 - 2,475/ 0 - 3,000/ 0 - 3,500
Max. bolt diameter	M22
Weight with battery pack (EPTA) (kg)	2.0 (M18 B5)
Kit included	No batteries supplied, No charger supplied, HD Box
Article number	4933493412