

415L
Punte elicoidali cilindriche serie lunga, in acciaio HSS-CO 5% rettificate
DIN 340
 $R \leq 1200 \text{ N/mm}^2$
 $HV \sim 800 \div 860$

	art.	L1 mm	L mm	Ø mm
004150236	415 L3,00	66	100	3,00
004150238	415 L3,50	73	112	3,50
004150240	415 L4,00	78	119	4,00
004150242	415 L4,50	82	126	4,50
004150244	415 L5,00	87	132	5,00
004150246	415 L5,50	91	139	5,50
004150248	415 L6,00	91	139	6,00
004150250	415 L6,50	97	148	6,50
004150252	415 L7,00	102	156	7,00
004150256	415 L8,00	109	165	8,00
004150260	415 L9,00	115	175	9,00
004150264	415 L10,00	121	184	10,00

