



 TEMPUS 5628

EN ISO 20345:2011 S1, P, SRC ASTM F2413-18 M/I/C SD 35 PR ASTM F3445-21 SR



FOR WORK AND LEISURE WITH PINK DETAILS

Light weight safety shoe with pink details for work and leisure. Breathable, sporty and comfortable with advanced shock absorbing with PORON XRD, protective toe cap and a soft and flexible nail penetration insert made of textile material. The well proven outsole has a very effective grip pattern and is made of a special nitrile rubber for high durability. The JALAS[®] Tempus shoes are ESD and antistatic certified to be used in ESD protected work environments.

CHARACTERISTICS	FUNCTIONS
• Excellent shock absorption • Excellent grip • Perfect fit • Extra comfortable • Very breathable • Extremely light	• Double shock absorption zones • Oil-resistant outsole • Anti-static properties • Ventilating insole • Low weight • Bellows tongue • Conforms with IEC 61340-5-1 (ESD) • Soft • Ergonomically shaped



PREVENTS RISK OF

Toe injuries, nail penetration, antistatic, slipping

PRIMARY ENVIRONMENTS OF USE

Indoors, environments with risk for outsole penetration, dry environments, clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes

CATEGORY Cat. II

NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile

FITTING Narrow/Regular

COLLECTION Tempus

UPPER MATERIAL Microfiber, Textile

TOECAP MATERIAL Steel

LINING MATERIAL Polyester, polyamide

INSOLE FX2 Pro Slim

INNERSOLE MATERIAL Textile, Soft EVA, Polyester-based conductive thread, Double shock absorption zones in Poron® XRD®

MIDSOLE MATERIAL EVA

OUTSOLE MATERIAL Nitrile rubber outsole

FASTENING Laces


COLOUR Black, Pink, White

NET WEIGHT, (SIZE 42) 0.93 kg

COMPLIANCE



TP TC 019:2011



EN ISO 20345:2011
S1, P, SRC

ASTM F2413-18
M/II/C
SD 35 PR

ASTM F3445-21
SR



ÖNORM Z 1259



DGUV 112-191

FEATURES



Anti-static properties



Ergothan Shock
Absorption System



ESD



Oil-resistant outsole



Steel toe cap



Nail protection in
plasma-treated
composite (PTC)
textile

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3½	4	5628-35	6408487544156
36	3	4	5	5628-36	6408487544200
37	4	5	6	5628-37	6408487544255
38	5	5½	6½	5628-38	6408487544309
39	6	6½	7½	5628-39	6408487544354
40	6½	7½	8½	5628-40	6408487544408
41	7	8	9	5628-41	6408487544453
42	8	9	10	5628-42	6408487544507

ejendals

Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com