

Features

- Portable Work Light
- With high quality SMD LED
- Waterproof IP66 rated
- Magnet, Hook for various occasions
- CE certified

RS PRO Torches

RS Stock No.: 0655945



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Ideal for professional construction engineering, plumbing & electrical renovation, automobile & machinery repair applications or wilderness exploration.
- Adopts high-quality SMD LED light source, adjustable brightness and uniform flood beam pattern with output of 660Lm.
- Waterproof IP66 rated, equipped with a strong magnet, hook, micro USB charging port for various occasions.

General Specifications

Torch Style	Straight
Lamp Type	LED
Luminosity	660lux
Range	10m
Beam Type	Flood
Switching Modes	High, Low, OFF
Light Colour	White
Number of LEDs	8
Colour	Red
Case Material	PC, TPE
Anti-Corrosive	No
Drop Resistance	2m

Modes Specifications

Parameters	High Mode	Low Mode / Strobe
Light Output	550lm	280lm
Run Time	4 hour	8.5 hours
Beam Distance	10m	8m

Electrical Specifications

Rechargeable	Yes
Plug Type	USB; Micro-USB
Batteries	3.7V 3350mAh Li-ion
Charging Time	Approx. 4.5 hours
LED Charging Indicator	Blue flashing-Charging, Blue light-Fully charged
Battery Indicator	Yes/Low power-Red
Switch Type	Two-stage switch

Mechanical Specifications

Length	19.1cm
Width	3.4cm
Head Diameter	3.3cm
Weight (with Batteries)	334g

Protection Category

IP Rating	IP66
------------------	------

Approvals

Compliance/Certifications	CE / UKCA
Standards Met	EN 55015; 61547
Hazardous Area Certification	ATEX; IECEx

