

daA1920-160um (S-Mount) - Basler dart

The Basler daA1920-160um (S-Mount) USB 3.0 camera with the Sony IMX392 CMOS sensor delivers 160 frames per second at 2.3 MP resolution. This model comes with a S-mount.



Specifications



General Information

Design-In Sample:	now
Series Production:	now
Order Number	108230

Sensor

Sensor Vendor	Sony
Sensor	IMX392
Shutter	Global Shutter
Max. Image Circle	1/2.3"
Sensor Type	CMOS
Sensor Size	6.6 mm x 4.2 mm
Resolution (HxV)	1920 px x 1200 px
Resolution	2.3 MP
Pixel Size (H x V)	3.45 µm x 3.45 µm
Frame Rate	160 fps
Mono/Color	Mono

Camera Data

Interface	USB 3.0
Pixel Bit Depth	8, 12 bits
Synchronization	■ software trigger

Camera Data

	■ hardware trigger ■ free-run
Image Processing	In-Camera Processing
Exposure Control	■ programmable via the camera API ■ hardware trigger
Digital Input	1
Digital Output	2
General Purpose I/O	2
Power Supply	■ Via USB 3.0 interface
Power Requirements (typical)	1.8 W

Housing

Housing Type	Board Level
Housing Size (L x W x H)	19.9 mm x 29.3 mm x 29 mm
Lens Mount	■ S-mount
Operating Temperature	0 - 50°C
Weight (typical)	15g

Conformity

Conformity	■ RoHS ■ USB3 Vision ■ CE ■ GenICam ■ KC ■ UL ■ FCC ■ EAC
------------	---

 share

 tweet

 share

 mail



eNewsletter

Regular updates on events and product innovations:

 Subscribe

Basler on the social networks

Keep in touch with us via the social networks:

