


1132936 HGPD-16-A Parallel gripper - Series: All



## 1132936 HGPD-16-A Parallel gripper - Series: All

| Pos. | Part no. | Type                                           | Note                                                                                      | Qty. | Unit |
|------|----------|------------------------------------------------|-------------------------------------------------------------------------------------------|------|------|
| A    | 1974941  | HGPD-16-A<br>Set of wearing parts              | Spare parts: 2, 3, 4, 9, 11, 13, 14, 15, 16, 18, 19, 20                                   | 1    | PC   |
| 1    |          |                                                | Not available<br>Grease using during assembly. See position 19                            | 2    | PC   |
| 2    |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 2    | PC   |
| 3    |          |                                                | Not available separately, see position A<br>Lubricate with Molykote BR2 during assembly   | 1    | PC   |
| 4    |          |                                                | Not available separately, see position A                                                  | 1    | PC   |
| 5    |          |                                                | Not available                                                                             | 5    | PC   |
| 6    |          |                                                | Not available                                                                             | 1    | PC   |
| 7    |          |                                                | Not available                                                                             | 2    | PC   |
| 8    |          |                                                | Not available<br>Grease using during assembly. See position 19                            | 1    | PC   |
| 9    |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 2    | PC   |
| 10   |          |                                                | Not available                                                                             | 1    | PC   |
| 11   |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 1    | PC   |
| 12   | 735821   | HGPT-16-A-B<br>Piston module                   | Attention, please order position 999 as well                                              | 1    | PC   |
| 13   |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 1    | PC   |
| 14   |          |                                                | Not available separately, see position A<br>Use locking compound. See position 20         | 1    | PC   |
| 15   |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 1    | PC   |
| 16   |          |                                                | Not available separately, see position A<br>Grease using during assembly. See position 19 | 2    | PC   |
| 17   |          |                                                | Not available                                                                             | 1    | PC   |
| 18   |          |                                                | Not available separately, see position A<br>Use locking compound. See position 20         | 4    | PC   |
| 19   | 665354   | LUB-KB1-SILIKONFREI-20ML<br>Lubricating grease | Only for piston chamber!                                                                  | 1    | PC   |
| 20   | 8181256  | CYBERBOND TM44 TB1ML<br>Adhesive bonding agent |                                                                                           | 1    | PC   |