


NUTR2052

Galet de roulement

Yoke type track rollers NUTR...-A, double row cylindrical roller bearings with particularly thick-walled outer ring, full complement cylindrical roller set and an inner ring, the outer ring is guided axially by the rolling elements, labyrinth seals on both sides

Information technique



Votre alternative produit actuelle

joint	2LB	Labyrinth seals on both sides
profile bague extérieure	IOP	Optimized INA-profile
dispositif de lubrification	IR	Via inner ring

dimensions principale & données de performance

d	20 mm	Alésage
D	52 mm	Diamètre extérieur
B	25 mm	Largeur, bague intérieure
C _{r w}	31.500 N	Charge dyn. de base, radiale
C _{0r w}	44.500 N	Charge stat. de base, radiale
C _{ur w}	5.800 N	Limite à la fatigue, radiale
n _{D G}	4.200 1/min	Vitesse pour une lubrification à la graisse
F _{0r per}	44.500 N	Charge radiale statique admissible
F _{r per}	38.000 N	Charge radial dynamique admissible sur bague extérieure
≈m	0,317 kg	Poids

Dimensions

C	24 mm	Largeur, bague extérieure
d ₂	27 mm	Diamètre d'arrêt rondelle de butée
r _{min}	1 mm	Dimension minimum de chanfrein
r _{1 min}	0,5 mm	Dimension minimum de chanfrein