

Technical data sheet

Article number:
924-00442

QDF5-6F

Product Group	Quick Connect Fully Insulated Female Funnel Entry 105 °C
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyamide 6.6 (PA66), Copper (CU)
Colour	Yellow (YE)
Application Range	Low Voltage
Conductor Size Range mm²	4.0-6.0 mm ²
Diameter (D)	6.6 mm
Halogen-free	Yes
Length (L)	26 mm
Length (L2)	14 mm
Max Current	24 A
Max Voltage	300 V
Operating Temperature	+105 °C
Package Content	50 pcs.
Package Content packed in	bag
REACH Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	9 mm
Width (W2)	6.7 mm

