



M18 FUEL™

M18 FCS552-0

M18 FUEL™ COMPACT CIRCULAR SAW

The M18 FUEL™ circular saw delivers the power to rip cut at the same feed rate of an equivalent AC circular saw, with the ability to cut 200 pieces of 90 mm x 35 mm pine stud on one 3.0 Ah HIGH OUTPUT™ battery as its optimised for HIGH OUTPUT™ technology

Magnesium shoe reduces weight and maximises durability

Durable metal rafter hang hook for work space management and safety

165 mm blade which gives a 57 mm depth of cut, enabling the saw to cut through a stack of 3x 18 mm OSB boards

Kitted with our DEK26 vacuum adaptor which will fit directly to all MILWAUKEE® dust extractors

Integrated LED light for workspace illumination

Integrated dust blower keeps cut line clear

Up to 50° bevel capacity

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Kit included

No batteries supplied, No charger supplied, No kitbox or bag supplied

Article number

4933493587