


32704 DPZ-25-80-P-A Twin cylinder - Series: All



32704 DPZ-25-80-P-A Twin cylinder - Series: All

Pos.	Part no.	Type	Note	Qty.	Unit
A	383824	DPZ - 25-P-A Set of wearing parts	Spare parts: 3, 5, 7, 9, 10	1	PC
1	343442	DPZ- 20- P-A Grooved nut	Tightening torque 10 Nm / 7.4 lbf ft Use locking compound 8181256 CYBERBOND TM44	2	PC
2	343427	DPZ- 25- P-A End plate		1	PC
3		DPZ-20/25/32-... Buffer element	Not available separately, see position A	1	PC
4	201028	J-26 Retaining ring		4	PC
5	338265	WIFC4-12X19X4,8-TPE-U Wiper seal	Lubricate with 684474 LUB-KC1 during assembly	2	PC
6	347349	ARA-12-S0118,5-BHS Piston rod	Tightening torque 15 Nm / 11.1 lbf ft	2	PC
7		B-23X1,5-N-NBR75 O-ring ISO3601	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
8	354371	DPZ- 25- P-A Bearing		2	PC
9		DSN- 25-P Cushioning ring	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
10		LEFC2-25X19X4-TPE-U Lip seal	Not available separately, see position A Lubricate with 684474 LUB-KC1 during assembly	4	PC
11	760706	DSNU- 25- PA ET Piston magnet		2	PC
12	209264	ISO 4017-M6X16-8.8 Hexagon head screw	Tightening torque 10 Nm / 7.4 lbf ft	1	PC
13	200601	DIN 439-B-M6-04 Hex nut		1	PC
14			Not available	1	PC
15	343435	DPZ-25 End cap		2	PC