


KERN 328-04

KERN

Milligram weights, F1, 10 mg, Platelet, stainless steel polished



Category

Brand	KERN
Product category	Individual weight
Product group	OIML F1
Product family	328

Measuring System

Test weight - nominal value	10 mg
Test weight - volume uncertainty (cm ³)	0,0001
Weight OIML class	F1
Test weight - volume (cm ³)	0,0012
Permissible tolerance according to OIML (+/-)	0,025 mg
OIML-compliant	✓
Test weight - Density (kg/m ³)	7960
Test weight - Density uncertainty (kg/m ³)	170

Construction

Shape weight	Platelet
Dimensions weight (W×D×H)	7,5×6×3 mm
Material	stainless steel polished
Adjustment method	Filing

Services (optional)

Article number for DAkkS calibration	962-454
Article number for guaranteed plus-deviation	921-454

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	7,5×6×3 mm
Shipping method	Parcel service
Net weight approx.	0,05 kg
Gross weight approx.	0,05 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	347-009-400
Case - Aluminium article number	317-009-600
Case - Wood article number	338-090-200

Product information

GTIN/EAN number	4045761240346
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

