

# KERN 333-024

**KERN**

Weight set, F2, 1 mg - 50 g, Knob, stainless steel fine turned, in plastic case



## Category

|                  |            |
|------------------|------------|
| Brand            | KERN       |
| Product category | Weight set |
| Product group    | OIML F2    |
| Product family   | 333        |

## Measuring System

|                             |             |
|-----------------------------|-------------|
| Test weight - nominal value | 1 mg - 50 g |
| Weight OIML class           | F2          |
| OIML-compliant              | ✓           |

## Construction

|                    |                             |
|--------------------|-----------------------------|
| Dimension (W×D×H)  | 250×210×75 mm               |
| Shape weight       | Knob                        |
| Material           | stainless steel fine turned |
| Number of weights  | 20                          |
| Case of weight set | in plastic case             |

## Services (optional)

|                                              |         |
|----------------------------------------------|---------|
| Article number for DAKkS calibration         | 962-401 |
| Article number for guaranteed plus-deviation | 921-401 |

## Packing & Shipping

|                              |                |
|------------------------------|----------------|
| Delivery time                | 1 d            |
| Dimensions packaging (W×D×H) | 250×210×75 mm  |
| Shipping method              | Parcel service |
| Net weight approx.           | 0,50 kg        |
| Gross weight approx.         | 0,50 kg        |
| Shipping weight              | 0,8 kg         |

Shipping volume weight 0,8 kg

## Optional cases

Case - Plastic article number 313-052-400

## Product information

|                      |                          |
|----------------------|--------------------------|
| GTIN/EAN number      | 4045761005617            |
| Trade number         | 84239090                 |
| REACH classification | no prohibited substances |

## Pictograms

### STANDARD



### OPTION

