


Telephone Outlets



Description

This uniquely shaped range of telephone outlets is easy to install, with clear bold terminal markings and is supplied in individual protective polybags suitable for display.

Features

- Contemporary designed profile
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- IDC terminals on UK version
- Screw terminals on RJ11
- Fixing screws attached to rear of plate
- Individually bagged
- 2-year guarantee

Range

Single Master	VP1352
Single secondary	VP1353

Technical Specification

Terminal Type	IDC – VC1352 VC1253 Screw – RJ11
Size	86 x 86 x 7mm (H x W x D)
Front plate material	Urea formaldehyde

Urea flammability classification UL94 grade V-0

No user serviceable parts

Back Boxes

Minimum recommended depth

	Metal Flush	Dry lining	Surface	
	25mm	35mm	25mm	33mm*
1g	DB162	DB2540	VP1221	VP1222
2g	DB163	DB2541	VP1223	VP1224

Standards

- OFTEL approved NS/G/23/L/100005

Terminal Capacity

- 2 Conductors per terminal (each 0.4mm ø nominal)