

M18 RADDAB+G2-O

M18™ JOBSITE RADIO DAB+

- High performance audio system - DAB+/ FM tuner with digital processor delivers high reception accuracy and signal clarity
- Digital Bluetooth® receiver, plays music up to 36 m away from your smartphone, computer or tablet
- Integrated handles and on board storage allow for easy transport and storage for phones
- Dual 8.89 cm woofers provide balanced & clear sound
- Dual high range tweeters deliver crisp highs
- Customisable equalizer for enhanced sound quality and 18-station preset
- Shock absorbing end caps and metal speaker grills protect from drops, water and debris on the jobsite
- Protected USB-C power outlet charges electronic devices in both AC and DC mode
- Powered by MILWAUKEE® M18™ batteries or AC outlet
- Up to 13 hours of run time with an M18™ REDLITHIUM™ 5.0 Ah battery pack



REDLITHIUM™



Tuning range FM (MHz)	87.5 - 108
Tuning range AM (kHz)	522 - 1620
Tuning range DAB+ (MHz)	174 - 239
Dimensions (Outer)(H x W x D / mm)	442 x 216 x 216
Weight with battery pack (EPTA) (kg)	4.6 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933492344