


KERN 356-89

KERN

Individual weight, OIML Class M2, 50 kg, Block, cast iron lacquered



Dimensions packaging (W×D×H) 310×155×192 mm

Shipping method Freight

Net weight approx. 50 kg

Gross weight approx. 50 kg

Shipping weight 50 kg

Shipping volume weight 1,8 kg

Product information

GTIN/EAN number 4045761248304

Trade number 84239090

REACH classification no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M2
Product family	356

Measuring System

Test weight - nominal value	50 kg
Test weight - volume uncertainty (cm ³)	595,12
Weight OIML class	M2
Test weight - volume (cm ³)	7042,2535
Permissible tolerance according to OIML (+/-)	8 g
OIML-compliant	✓
Test weight - Density [Min] (OIML)	2300
Test weight - Density (kg/m ³)	7100
Test weight - Density uncertainty (kg/m ³)	600

Construction

Shape weight	Block
Dimensions weight (W×D×H)	310×155×192 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-646
--------------------------------------	---------

Packing & Shipping

Delivery time	2 d
---------------	-----