

KERN 316-07

KERN

Individual weight, OIML Class E2, 100 g, Compact form, stainless steel polished



Article number for guaranteed plus-deviation 921-337

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	22×22×35 mm
Shipping method	Parcel service
Net weight approx.	0,10 kg
Gross weight approx.	0,10 kg
Shipping weight	0,1 kg
Shipping volume weight	0,1 kg

Optional cases

Case - Plastic article number	317-070-400
Case - Aluminium article number	317-070-600
Case - Wood article number	317-070-100

Product information

GTIN/EAN number	4045761094895
Trade number	84239090
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML E2
Product family	316

Measuring System

Test weight - nominal value	100 g
Test weight - volume uncertainty (cm ³)	0,1563
Weight OIML class	E2
Conformity assessment possible	no
Test weight - volume (cm ³)	12,5
Permissible tolerance according to OIML (+/-)	0,16 mg
OIML-compliant	✓
Test weight - Density [Min] (OIML)	7810
Test weight - Density [Max] (OIML)	8210
Test weight - Density (kg/m ³)	7950
Test weight - Density uncertainty (kg/m ³)	140

Construction

Shape weight	Compact form
Dimensions (Ø×H)	22×35 mm
Material	stainless steel polished
Adjustment method	Polishing

Services (optional)

Article number for DAkkS calibration	962-337
--------------------------------------	---------