

B-VE 200R

Pressed steel fixed castor, medium duty design, with top plate fitting, wheel, with standard solid rubber tyre, with pressed steel rim

EAN 4047526278342

ID 278341

Customs tariff number 87169090



Bracket: B series

- pressed steel, zinc-plated, blue-passivated, Cr6-free

Wheel: VE series

- tyre: standard solid rubber, hardness 80 Shore A, colour black
- rim: pressed steel, zinc-plated, blue-passivated, Cr6-free

Other features:

- chemical resistance to many aggressive substances, except oils
- operating temperature: -25 °C to +80 °C, reduced load capacity over +60 °C



Technical data:

Wheel Ø (D)	☞	200 mm
Wheel width	⏏	50 mm
Load capacity at 4 km/h	⚖	205 kg
Load capacity (static)	⚖	515 kg
Bearing type	⦿	roller bearing
Total height (H)	⌀	235 mm
Mounting type		top plate
Plate size	📏	140 x 110 mm
Bolt hole spacing	📏	105 x 75–80 mm
Bolt hole Ø	🔧	11 mm
Temperature resistance min		-25 °C
Temperature resistance max		80 °C
Tread and tyre hardness		80 Shore A
Unit weight	📊	2.8 kg
Non-marking		✗
Non-staining		✗
Antistatic	⚡	✗
ESD		✗
Electrically conductive	⚡	✗
Corrosion-resistant		✗
Heat-resistant	🔥	✗
Suitable for autoclaves		✗
Suitable for machine washing		✗

Tread and tyre hardness

■ ■ ■ □ □ 80 Shore A

Rolling resistance


■ ■ □ □ □ satisfactory

Wear resistance

■ □ □ □ □ sufficient

Operating noise / floor surface preservation

■ ■ ■ ■ □ very good



Product references



Corresponding swivel castor LE-VE 200R



Wheel used VE 200/20R