

1498/SP250

Conventional battery charger / starter, 12/24 V

CE

Safety and reliability in any situation thanks to high-quality electronics.

Features:

- For lead-acid storage batteries
- Charging current selector
- Ammeter
- Thermostatic long start protector
- Short-circuit protection fuse
- Reverse polarity protector

 10,7 Kg

Technical data:

- Power supply (1ph): 230 V - 50/60 Hz
- Power: 650 W
- Voltage: 12/24 V
- Maximum current: 27 A
- Charging current: 18 A
- Max. boost current: 200 Acc
- Starting current: 135 A
- Charging capacity: 270 Ah 15h
- Charging positions: 2 + boost



	art.	L mm	P mm	H mm
014980746	1498/SP250	220	235	335