

5935VG/1MB
Assortment of 98 tools for car repairs in EVA foam trays

Car repairs

		art.
	059351321	5935VG/1MB

- n. 21 **42:** combination wrenches
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- n. 8 **55:** double open end wrenches 6x7-8x9-10x11-12x13-14x15
16x17-18x19-20x22 mm
- n. 1 **1048N:** slip joint pliers, slip-proof PVC coated handles 250 mm
- n. 4 **1260:** screwdrivers for slotted head screws  3x75-4x100-5x125-6,5x150 mm
- n. 3 **1262:** screwdrivers for cross head Phillips® screws  PH0x60-PH1x80--PH2x100 mm
- n. 6 **1267TX:** drivers for Torx® head screws  T8-T10-T15-T20-T25-T30
- n. 9 **96BPC/SC9:** ball head offset hexagon key wrenches 
- n. 6 **96T:** offset hexagon key wrenches  2-2,5-3-4-5-6
- n. 1 **1052:** self - locking pliers 240 mm
- n. 19 **920A:** 1/2" square drive hexagon sockets 
10-11-12-13-14-15-16-17-18-19-20-21-22-23-24-26-27-30-32 mm
- n. 1 **920/21:** 1/2" drive extension bar 125 mm
- n. 1 **920/22:** 1/2" drive extension bar 250 mm
- n. 1 **920/25:** 1/2" drive universal joint
- n. 1 **920/42:** 1/2" drive sliding T-handle
- n. 1 **920/55:** 1/2" reversible ratchet 
- n. 5 **920PE:** 1/2" socket drivers for hexagon screws  5-6-8-10-12 mm
- n. 1 **1032:** circlip pliers straight, internal  180 mm
- n. 1 **1034:** circlip pliers bent, internal  170 mm
- n. 1 **1036:** circlip pliers straight, external  175 mm
- n. 1 **1038:** circlip pliers bent, external  175 mm
- n. 1 **35:** flat chisels, ribbed type 200 mm
- n. 1 **1084BM:** Heavy-duty diagonal cutting nippers  160 mm
- n. 1 **1150BM:** combination pliers bright chrome-plated, bi-material handles  180 mm
- n. 1 **1166BM:** Extra-long needle nose pliers  160 mm
- n. 1 **1370:** engineer's hammer 500 g
- n. 1 **1390:** soft face hammer Ø 35 mm



MB12



MB39



MB46



MB12



MB39



MB46