



Maintenance panel

PAN-MAIN

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:13





DESCRIPTION

Maintenance panel

Complete screen-printed wall panel with tools, defined according to the service.
Available with a background colour of your choice with black imprints.

Panel dimensions: 1000 x 600 mm.

Round perforations.

Used with hooks 920C1 to 920C9.

Set of hooks included with the selection of tools.

Wall attachment rail supplied with the panel.

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:13



SPECIFIC DATA

Designation	COMPLETE MAINTENANCE PANEL WITH TOOLS
Sales reference	PAN-MAIN
Weight (kg)	20.000
Guarantee	O SAM TOOL guarantee.

Guarantee applied

O | SAM TOOL guarantee.

Guarantee without time limit on the tools used under normal conditions.

[>> Find out more](#)

Toolset

	x 2	Straight 3/8" extensions J-2... Ref : J-208 - J-210
	x 1	3/8" impact extension NJ-21... Ref : NJ-220
	x 1	3/8" drive extension - T handle 2216
	x 2	Spark plug mounting tool 385... Ref : 3851 - 3852
	x 2	Flexible screwdriver 6 mm 23-... Ref : 23-07 - 23-08
	x 4	Impact sockets 1/2" "long 12 points thin 19143-...M Ref : 30 - 32 - 35 - 36

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2026-08-07 13:59:13



	x 2	Impact sockets 1/2" "- 40mm and 41mm 19143-... Ref : 40 - 41
	x 2	Open piping sockets 3/8" 2217-... Ref : 17 - 19
	x 1	Torque wrench with fixed ratchet 1/4" 5-25 nm 220-80 Ref : 222-81
	x 1	Spark plug long socket 3/8" 14 mm 3813-... Ref : 3813-140
	x 1	Sign banner holder 450mm 921E
	x 1	Box of 1/4" impact wrench for removing sparkplugs, S1 series 1126-90P
	x 3	T-handle wrench, extra long 97-... Ref : 10 - 11 - 12
	x 4	Diesel pre-heat spark plug 3/8" socket with joint BCP-... Ref : 8 - 9 - 10 - 12
	x 1	180 to 720 mm telescopic magnet 344-4
	x 1	Telescopic mirror 344-5
	x 3	Petrol spark plug 3/8" socket with joint BDC-...-JC Ref : 14 - 16 - 21
	x 2	Petrol spark plug 3/8" socket BD-...-J Ref : BD-14-JC12 - BD16-JC12
	x 1	Magnetiser / demagnetiser MAGDEM
	x 1	Spare chain for exhaust pipe cutter 913-7-C