

DeWalt DCD703D2-B1

12V Brushless XTREME 5in1 Drill 2.0Ah x2

Introduction

The **DCD703D2-B1 12V MAX* XR® Brushless Multi-Head Drill/Driver Kit** is an ultra-compact, versatile solution for precision drilling and fastening in tight spaces. Driven by a powerful brushless motor, it features a unique 4-in-1 interchangeable chuck system that easily swaps between a standard 3/8" chuck, a 1/4" hex quick-release holder, an offset hex chuck, and a right-angle hex chuck. With a short 5.1-inch body, a 2-speed transmission, and a 15-position clutch, it offers exceptional access and control. This complete kit includes two 2.0Ah batteries, a charger, and a storage bag, making it ideal for cabinet installers, electricians, and carpenters.

Key Features

- Pro-grade efficiency
- High transmission speeds
- Compact & lightweight design
- Integrated LED light for visibility
- Drill and fasten in confined spaces
- 3 years warranty

Specifications Table

Specification	Details
No Load Speed	0 – 1500 rpm
Power Output	250 W
Voltage	12 V
Tool Holder	6.35 mm (1/4")
Max. Drilling Capacity (Wood / Metal)	20 mm / 10 mm
Battery Capacity	2.0 Ah
Chuck Capacity	10 mm
Max Torque (Soft)	25.5 Nm
Max Torque (Hard)	57.5 Nm
Unit Weight	0.73 kg